



# Bassi Logic™

## A Monumental Leap for Conservative Endodontics.

### Next-Gen Heat Treatment

At Bassi, we use a proprietary heat treatment process for achieving the strongest cyclic fatigue and highest torsional resistance while maintaining sharpness. Allowing for conservative shaping—safely and with confidence.

### Cuts Like Steel

Now there is a heat treated NiTi file that cuts like stainless steel. Studies have shown Bassi Logic™ completes instrumentation in a third less time than leading single file systems†.

### Structure-Preserving Flexibility

Tightly follow the contour of any root with confidence—no longer is flaring, brushing or straight line access needed. Bassi Logic™ files have been shown to have significantly greater resistance to cyclic fatigue and high torsional resistance compared with other single file systems\*.

### Single-Shaping File Simplicity

Bassi Logic™ is a single-file shaping system that can be used in reciprocating or continuous rotary motors and is shown to have greater performance and safety than leading single-file reciprocating systems.

### Shaped to Clean

Every file is designed with a specific helix that promotes the highest cutting efficiency and reduces the screwing effect as much as possible.

†Brazilian Dental Journal (2016) 27(2): 217-222

\*IEJ Iranian Endodontic Journal 2017;12(4): 468-473




# 30%

Faster Instrumentation

# 3.5x

Cyclic Fatigue Resistance



VS



“I’ve been using Logic files since their introduction to the market, and the results are the best possible. The new .03 taper series impresses me with its working safety, allowing great preservation of dentinary structure, and can be used in any type of anatomy.”

Augusto Kato, DDS

 **Ba ssi**<sup>™</sup>  
BassiEndo.com  
F012019A

# Bassi Logic™

Conservative. Efficient. Advanced.

## Bassi Logic™ Individual Files



Logic™ Glidepath  
4 pack

15/03 | 15/05

25/01 | 40/01  
30/01 | 45/01  
35/01 | 50/01



Logic™ Shaping  
4 pack

25/03 | 25/04 | 25/05 | 25/06  
30/03 | 30/05  
35/03 | 35/05  
40/03 | 40/05



Logic™ Retreatment  
4 pack

20/06 | 25/08 | 30/10

## Activation & Obturation



Bassi™ Clean  
48 pack



Hand Plugger Kit  
4 pack

## Bassi Logic™ Procedure Kits



Logic™ Shaping  
& Glidepath Kit  
2 pack

25/01 | 30/01 | 35/01 | 40/01  
25/05 | 30/05 | 35/05 | 40/05



Logic™  
Retreatment Kit  
3 pack

20/06  
25/08  
30/10



Logic™  
Manual Kit  
2 pack | 3 pack

25/01 | 35/01 | 40/01  
15/05 | 35/05 | 40/05  
25/06



Universal Heat  
Plugger



"After 4 years using the Logic system every day, I can say there isn't a safer and more efficient instrument available in the market. Everybody wins - patients, professionals and Endodontics itself."

Hugo Bastos, DDS